

SURGICRYL[®]

MONOFAST

POLYGLYCAPRONE 25



Type	Monofilament
Composition	Polyglycaprone 25, a copolymer made of 75% glycolide and 25% ε-caprolactone
Coating	None
Colour	Violet / Beige - undyed
Tissue reaction	Minimal
Absorption	The hydrolytic action by which the material is broken down results in total absorption in approximately 90 to 120 days. Approximately 60% of tensile strength remain after 7 days.
Presentation	Box with 12 sutures



*For quality
&
safety*

smi

www.sutures.be

SURGICRYL[®]

MONOFAST

POLYGLECAPRONE 25

CHARACTERISTICS

- ✓ High tensile strength
- ✓ Synthetic
- ✓ Breaks down by hydrolysis
- ✓ Monofilament with microscopic uniform diameter

- ✓ Pliability and softness

- ✓ Hermetically sealed packing

BENEFITS

- Excellent tissue support
- Minimal tissue reaction
- Predictable absorption rate

- Soft passage through the tissues without sawing, tissue drag and trauma
- Absence of capillarity (no support of bacterial growth)
- Excellent knot tie down

- Good handling properties
- Easy and secure knotting


- Guaranteed seal and product sterility

INDICATIONS Superficial soft tissue and/or ligation
especially in General surgery
Skin closure
Plastic surgery
Gastrointestinal surgery
Gynaecology
Urology

CONTRAINDICATIONS Cardiovascular surgery
Neurosurgery
Ophthalmic surgery

Being absorbable not to use when an extended wound support is required.

Caution in patients with delayed wound healing (e.g. compromised immune system).







Without needle 	Metric	USP	Length		Order number
	3	2/0	150 cm	<i>violet</i>	16300015
	3.5	0	150 cm	<i>violet</i>	16350015
	4	1	150 cm	<i>violet</i>	16400015
	5	2	120 cm	<i>violet</i>	16500012
	5	2	150 cm	<i>violet</i>	16500015

Without needle 	Metric	USP	Length		Order number
--	--------	-----	--------	--	--------------

Ligapack



5	2	250 cm	<i>violet</i>	16500025
---	---	--------	---------------	----------

Round bodied taper point 	Metric	USP	Length		Order number
HR 13 mm 	0.7	6/0	45 cm	<i>violet</i>	16070113
	1	5/0	45 cm	<i>violet</i>	16100113
	1.5	4/0	75 cm	<i>violet</i>	16150113
HR 17 mm 	1	5/0	45 cm	<i>violet</i>	16100117
	1.5	4/0	75 cm	<i>violet</i>	16150117
	2	3/0	75 cm	<i>violet</i>	16200117
HR 22 mm 	1.5	4/0	75 cm	<i>violet</i>	16150122
	2	3/0	75 cm	<i>violet</i>	16200122
HR 26 mm 	1.5	4/0	75 cm	<i>violet</i>	16150126
	2	3/0	75 cm	<i>violet</i>	16200126
	3	2/0	75 cm	<i>violet</i>	16300126
	3.5	0	75 cm	<i>violet</i>	16350126
	4	1	75 cm	<i>violet</i>	16400126
HR 30 mm 	2	3/0	75 cm	<i>violet</i>	16200130
	3	2/0	75 cm	<i>violet</i>	16300130
	3.5	0	75 cm	<i>violet</i>	16350130
	4	1	75 cm	<i>violet</i>	16400130

1/2 Circle



Round bodied taper point



1/2 Circle



			Metric	USP	Length		Order number	
HR 36 mm			3	2/0	75 cm	<i>violet</i>	16300136	
			3.5	0	90 cm	<i>violet</i>	16350136	
			4	1	90 cm	<i>violet</i>	16400136	
		HR 40 mm		3	2/0	75 cm	<i>violet</i>	16300140
				3.5	0	90 cm	<i>violet</i>	16350140
				4	1	90 cm	<i>violet</i>	16400140
HR 48 mm			3.5	0	90 cm	<i>violet</i>	16350148	
			4	1	90 cm	<i>violet</i>	16400148	





Reverse cutting










3/8 Circle







			Metric	USP	Length		Order number
DS 12 mm			0.7	6/0	45 cm	<i>undyed</i>	16071512
			1	5/0	45 cm	<i>undyed</i>	16101512
			1	5/0	45 cm	<i>violet</i>	16101512V
DS 12 mm Easy Pass			0.7	6/0	50 cm	<i>undyed</i>	16071512P
			1	5/0	50 cm	<i>undyed</i>	16101512P
			1.5	4/0	50 cm	<i>undyed</i>	16151512P
DS 16 mm			1	5/0	75 cm	<i>undyed</i>	16101516
			1.5	4/0	75 cm	<i>undyed</i>	16151516
			2	3/0	75 cm	<i>undyed</i>	16201516
DS 16 mm Easy Pass			1	5/0	50 cm	<i>undyed</i>	16101516P
			1.5	4/0	50 cm	<i>undyed</i>	16151516P
		DS 19 mm			1	5/0	45 cm
	1.5			4/0	75 cm	<i>undyed</i>	16151519
	1.5			4/0	75 cm	<i>violet</i>	16151519V
DS 19 mm Easy Pass			2	3/0	75 cm	<i>undyed</i>	16201519
			3	2/0	75 cm	<i>undyed</i>	16301519
			1.5	4/0	50 cm	<i>undyed</i>	16151519P
DS 24 mm			2	3/0	50 cm	<i>undyed</i>	16201519P
			2	3/0	75 cm	<i>undyed</i>	16201524
			3	2/0	75 cm	<i>undyed</i>	16301524

Reverse cutting 		Metric	USP	Length	Order number
3/8 Circle 	DS 26 mm 	1.5	4/0	75 cm	<i>undyed</i> 16151526
		2	3/0	75 cm	<i>undyed</i> 16201526
		2	3/0	75 cm	<i>violet</i> 16201526V
	DS 40 mm 	3	2/0	75 cm	<i>undyed</i> 16301526
		3	2/0	75 cm	<i>violet</i> 16301526V
		3.5	0	75 cm	<i>undyed</i> 16351540
		4	1	75 cm	<i>undyed</i> 16401540

Reverse cutting 		Metric	USP	Length	Order number
1/2 Circle 	HS 36 mm 	3	2/0	75 cm	<i>undyed</i> 16301436
		3.5	0	75 cm	<i>undyed</i> 16351436
	HS 40 mm 	4	1	90 cm	<i>undyed</i> 16401440

Cutting 		Metric	USP	Length	Order number
Straight 	GS 60 mm 	2	3/0	75 cm	<i>undyed</i> 16202160
		3	2/0	75 cm	<i>undyed</i> 16302160

Blunt 		Metric	USP	Length	Order number
1/2 Circle 	HRB 40 mm 	3.5	0	90 cm	<i>violet</i> 16351840
	HRB 48 mm 	4	1	90 cm	<i>violet</i> 16401848